

FF6SSTB



33.5" x 23.63" x 23.63" (H x W x D)

Freestanding counter height all-refrigerator for general purpose use, auto defrost w/stainless steel wrapped door, towel bar handle, and white cabinet

Highlights:

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Automatic defrost ensures minimum user maintenance

Includes door storage and adjustable shelves

Product Features:

Slim counter height dimensions	Slim 24" footprint with full 5.5 cu.ft. capacity
Automatic defrost	Reduced maintenance with auto defrost system
Stainless steel wrapped door	Durable design with lasting elegance
Stainless steel towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Door storage	Keep large bottles and condiments right on the door for easy access
Crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer

FF6SSTB Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.63"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"

Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

