

# FF7BIFR



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS door frame for slide-in panels and a white cabinet

## Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door frame accepts slide-in panels for a custom look

Deep shelf space accommodates large trays

## Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used as a freestanding model
Stainless steel door frame	Slide a panel into the frame to match your unit to other cabinets (panel size: 23" W x 28" H at up to 1/4" thick)
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
Deep shelf space	Interior accommodates large trays up to 19 1/2" x 15 1/2"

## FF7BIFR Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.75"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	45.63"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"

Compressor Step Width	20.0"
Compressor Step Depth	6.0"

