

FF7LBLSSH



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/SS wrapped door, horizontal handle, lock, and black cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Factory-installed lock provides security you can count on

Stainless steel door complete with stylish horizontal handle

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Fully finished cabinet	Allows the refrigerator to be used as a freestanding model
Stainless steel door	Durable design with lasting elegance
Professional horizontal handle	Add sleek style in stainless steel with a horizontal handle at the top
Slim undercounter dimensions	Ideal 24" footprint offers full 5.5 cu.ft. storage capacity in a slim fit
Factory installed lock	Keyed lock for a secure interior
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Automatic defrost	Reduced user maintenance with automatic defrost

FF7LBLSSH Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	118.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"

Compressor Step Depth

