

# FF7LSSHV



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/lock, SS wrapped door, thin handle, and white cabinet

## Highlights:

Commercially approved for use in foodservice establishments

Factory-installed lock provides security you can count on

Stainless steel door complete with sleek handle for modern luxury

Deep shelf space accommodates large trays

## Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Fully finished white cabinet	Allows the refrigerator to be used freestanding
Slim counter height dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Stainless steel wrapped door	Durable design with lasting elegance
Professional stainless steel handle	Thin 14mm diameter on vertical stainless steel handle
Factory installed lock	Keyed lock for a secure interior
Automatic defrost	Reduced user maintenance with automatic defrost
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

## FF7LSSHV Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"

Compressor Step Width

Compressor Step Depth

