

# FF7LSSTB



33.5" x 23.63" x 23.63" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/lock, SS wrapped door, towel bar handle, and white cabinet

### Highlights:

Commercially approved for use in foodservice establishments

Automatic defrost minimizes user maintenance

Factory-installed lock provides security you can count on

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

### Product Features:

|                                |   |
|--------------------------------|---|
| Commercially approved          | ETL-S listed to NSF-7 Standards for use in commercial establishments  |
| Automatic defrost              | Reduced user maintenance with automatic defrost   |
| Fully finished cabinet         | Allows the refrigerator to be used as a freestanding model  |
| Factory installed lock         | Keyed lock for a secure interior  |
| Slim counter height dimensions | Less than 24 inches wide to fit tight spaces  |
| Stainless steel wrapped door   | Durable design with lasting elegance  |
| Professional towel bar handle  | Curved handle in brushed stainless steel offers a sturdy grip with professional elegance                      |
| Adjustable shelves             | Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up |
| One piece interior liner       | Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices                           |

**FF7LSSTB Specifications:**

| Overview                   |                    |
|----------------------------|--------------------|
| Height                     | 33.5"              |
| Width                      | 23.63"             |
| Depth                      | 23.63"             |
| Depth with Handle          | 25.13"             |
| Depth with door at 90°     | 46.0"              |
| Capacity                   | 5.5 cu.ft.         |
| Defrost Type               | Automatic          |
| Door                       | Stainless Steel    |
| Cabinet                    | White              |
| US Electrical Safety       | UL                 |
| Canadian Electrical Safety | ULC                |
| Sanitation                 | ETL-S              |
| Amps                       | 1.3                |
| Voltage/Frequency          | 115 V AC/60 Hz     |
| Shipping Weight            | 113.0 lbs.         |
| Parts & Labor Warranty     | 1 Year             |
| Compressor Warranty        | 5 Years            |
| Refrigerator Features      |                    |
| Door Swing                 | RHD                |
| Reversible                 | Factory Reversible |
| Shelf Type                 | Wire               |
| Shelf Qty                  | 3                  |
| Adjustable Shelves         | Yes                |
| Thermostat Type            | Dial               |
| Fan Type                   | Exterior           |
| Refrigerant Type           | R134a              |
| Refrigerant Amount         | 1.8                |
| High Side PSI              | 285.0              |
| Low Side PSI               | 70.0               |
| Level Legs Qty             | 4                  |
| Interior Light             | Yes                |
| Dimensions                 |                    |
| Interior Height            | 27.75"             |
| Interior Width             | 20.0"              |
| Interior Depth             | 17.5"              |
| Compressor Step Height     | 7.0"               |

Compressor Step Width  
Compressor Step Depth

