

FS407L7SSTBADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA compliant 20" wide all-freezer, -20° C capable with a lock, stainless steel door, towel bar handle and white cabinet

Highlights:

32" height for use in ADA compliant settings

ETL-S listed for commercial use

-20° C capable with interior slide-out drawers for easy storage

Factory installed lock provides security you can count on

Product Features:

ADA compliant	32" high meets ADA guidelines
Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	2.8 capacity inside a slim footprint
Factory installed lock	Top-mounted for convenient security
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable 304 grade wrapping
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability

FS407L7SSTBADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Stainless Steel
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

