

# FS407LBI



33.5" x 19.25" x 21.38" (H x W x D)

20" wide built-in undercounter all-freezer for general purpose use, -20° C capable with a lock and white exterior

## Highlights:

Slim 20" width is ideal for any setting

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

-20° C capable with interior slide-out drawers for easy storage

## Product Features:

Slim 20" width	2.8 capacity inside a slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Manual defrost	Efficient performance with reliable temperature stability
-20° capable	Low temperature capability ideal for certain sensitive items
Pull-out drawers	Four clear baskets for convenient and separated storage
Adjustable thermostat	Rear mounted to prevent accidental adjustments

**FS407LBI Specifications:**

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Yes
Height Adjustable	1
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

