

FS407LBI7IFADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA Compliant 20" wide built-in undercounter all-freezer, -20° C capable with a lock and integrated door frame for full overlay panels

Highlights:

32" height fits under lower ADA compliant counters

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

-20° C capable with interior slide-out drawers for easy storage

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	2.8 capacity inside a slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Integrated door frame	Stainless steel door frame accepts overlay panels for users to create a custom look over the front (panel size: 19 1/2" W x 31 1/2" H and at least 3/4" thick)
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability

FS407LBI7IFADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Panel-Ready
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

