

FS408BL7



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide counter height all-freezer, -20° C capable with a lock and black exterior

Highlights:

-20° C capable with interior slide-out drawers for easy storage

Slim 20" width is ideal for any setting

Includes a hospital grade cord with a 'green dot' plug

ETL-S listed for commercial use

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	2.8 capacity inside a slim footprint
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Manual defrost	Efficient performance with reliable temperature stability
-20° capable	Low temperature capability ideal for certain sensitive items
Pull-out drawers	Four clear baskets for convenient and separated storage

FS408BL7 Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Black
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Yes
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

