

# FS408BLBI7SSHV



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter all-freezer, -20° C capable with a lock, stainless steel door, thin handle and black cabinet

## Highlights:

Flexible design allows built-in or freestanding use in 20" wide spaces

ETL-S listed for commercial use

-20° C capable with interior slide-out drawers for easy storage

Factory installed lock provides security you can count on

## Product Features:

Slim 20" width	2.8 capacity inside a slim footprint
Commercially listed	ETL-S listed to NSF standards for commercial use
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Stainless steel wrapped door	Durable 304 grade wrapping
Professional handle	Thin 14mm diameter on vertical stainless steel handle
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability

**FS408BLBI7SSHV Specifications:**

<b>Overview</b>	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	2.8 cu.ft.
Defrost Type	Manual
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	298.0kWh/year
Amps	1.6
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
<b>Freezer</b>	
Door Swing	RHD
Reversible	Factory Reversible
Height Adjustable	1
Interior Height	26.38"
Interior Width	14.0"
Interior Depth	16.75"
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	3.0 oz.
High Side PSI	210.0
Low Side PSI	105.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	4

