

# HNC SERIES

## COUNTERTOP REFRIGERATED DISPLAY CASE

### STAINLESS STEEL SERIES

Item # \_\_\_\_\_

Project: \_\_\_\_\_

Qty: \_\_\_\_\_

\*AutoCad available on KCL

HNC SERIES

10/10

Item # 13245

#### DIMENSIONS


W x D x H

**HNC-120BA-R(L)-S**  
47.2 x 13.6 x 11

**HNC-150BA-R(L)-S**  
59.1 x 13.6 x 11

**HNC-180BA-R(L)-S**  
70.9 x 13.6 x 11

**HNC-210BA-R(L)-S**  
82.7 x 13.6 x 11



### HNC-210BA-R-S

Shown

- Top glass angles down
- Ceiling easier to clean
- NSF approved thermometer
- Plate space on top of unit, 5.6 inches
- Large diameter 1 inch drains at front
- Larger front to back interior, 11 inches
- Interior floor has a radius at all four sides
- Self-contained refrigeration unit - easy to install
- Condenser airflow is in the back and out the side
- Large diameter upper evaporator with tin plating
- Larger condenser face area improves cooling performance
- Slightly taller doors with plastic seal at end, opposite of the handle
- Solid food plates with radius groove to fit sushi foods
- Food plates can be turned upside down and used to improve cooling performance
- R-134A Refrigerant

#### Model Name

**HNC - 120BA - R/L - S** — Stainless Steel

High Grade

Counter Showcase

Width (cm)

120, 150, 180, 210

Unit Location  
R: Unit on right  
L: Unit on left

USA Model

Development Order  
Starts from A



ISO9001-ISO14001

#### Warranty

Warranty valid in United States, Canada, Puerto Rico, & U.S. Territories. Contact factory for warranty in other countries.

**One Year** - Parts & Labor on entire unit.

**Two Year** - Parts & Labor on compressor, evaporator, air-cooled condenser.

**Five Year** - Parts on: Compressor; Air-cooled condenser.

© HOSHIZAKI AMERICA, INC.

618 Hwy. 74 S., Peachtree City, GA 30269

TEL 1-800-438-6087

FAX 1-800-345-1325

www.hoshizaki.com



# H

# hoshizaki

## HNC SERIES COUNTERTOP REFRIGERATED DISPLAY CASE

- HNC-120BA-R(L)-S
- HNC-150BA-R(L)-S
- HNC-180BA-R(L)-S
- HNC-210BA-R(L)-S

- Right or left handed
- Right or left handed
- Right or left handed
- Right or left handed


### REFRIGERATED DISPLAY CASE

Model	HNC-120	HNC-150	HNC-180	HNC-210
AC Supply Voltage	1 Phase 115V 60Hz			
Power Supply Capacity	0.47KVA (4.7A)			
Rated Amperage	3.2A			
Starting Amperage	13A			
Electric Consumption	195W			
Saturation Temperature	Approximately 39°F (Ambient Temp. 80°F, No Load)			
Net Capacity	1.48ft <sup>3</sup>	2.01ft <sup>3</sup>	2.54ft <sup>3</sup>	3.07ft <sup>3</sup>
Ambient Temperature	50 - 80° F			
Voltage Variation	Rated Voltage ± 10%			
Exterior Dimensions (W)(D)(H)	47.2" 13.6" 11"	59.1"	70.9"	82.7"
Interior Dimensions (W)(D)(H)	33.3" 11.3" 6.2"	45.1"	56.9"	68.7"
Exterior	Clear Glass, ABS Plastic, PVC Plastic, Stainless Steel			
Interior	Clear Glass, ABS Plastic, Stainless Steel			
Refrigeration System	Convection Cooling			
Sliding Door	2 Pieces	4 Pieces		
Plate Space (Top of HNC)	5.6" for food plate to rest upon top of case			
Shipping Weight (Lbs.)	86	101	117	132
Shipping Dimensions (W)(D)(H)	51.2" 16.9" 18.6"	63"	74.8"	86.6"
Accessories	3 Pieces	4 Pieces	5 Pieces	6 Pieces
Food Mount	4 Pieces	4 Pieces	4 Pieces	4 Pieces
Plug	1 Piece	1 Piece	1 Piece	1 Piece
Vinyl Hose	2 Pieces	2 Pieces	2 Pieces	2 Pieces
Joint				

\*Refrigerated Display Case - Not for overnight storage




**HNC-120BA-L(R)-S**  
W x D x H  
47.2" x 13.6" x 11"



**HNC-150BA-L(R)-S**  
W x D x H  
59.1" x 13.6" x 11"



**HNC-180BA-L(R)-S**  
W x D x H  
70.9" x 13.6" x 11"



**HNC-210BA-L(R)-S**  
W x D x H  
82.7" x 13.6" x 11"

### ELECTRICAL/HNC SERIES-STAINLESS STEEL

- I115V60/1



© HOSHIZAKI AMERICA, INC.

618 Hwy. 74 S., Peachtree City, GA 30269

### OPERATING LIMITS

- Ambient Temp Range 50 - 80°F
- Voltage Range 104 - 126V
- Saturation Temp 39°F

### SERVICE

- Removable/cleanable air filters

TEL 1-800-438-6087

FAX 1-800-345-1325

www.hoshizaki.com

Printed in U.S.A.

