

SCR500BL7SH



33.25" x 19.38" x 22" (H x W x D)

Commercially listed 20" wide glass door all-refrigerator for freestanding use, auto defrost with a lock, long towel bar handle, and black cabinet

Highlights:

ETL-S listed for commercial use

Slim 20" width is ideal for any setting

Glass door offers full display of interior

Factory installed lock provides security you can count on

Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Commercially listed	ETL-S listed to NSF standards for commercial use
Fully finished black cabinet	Allows the unit to be used freestanding
Glass door	Heat resistant design offers full view of interior
Factory installed lock	Keyed security on the refrigerator door
Professional handle	16" long curved towel bar handle in brushed stainless steel
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup



SCR500BL7SH Specifications:

Overview	
Height	33.25"
Width	19.38"
Depth	22.0"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	60.0 lbs.
Shipping Weight	83.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Wheel Qty	2
Interior Light	Yes
Dimensions	
Interior Height	29.0"
Interior Width	17.0"
Interior Depth	17.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com