

# SCR600LBITB



33.5" x 23.63" x 23.6" (H x W x D)

Commercially listed built-in undercounter glass door all-refrigerator with white cabinet, stainless steel towel bar handle, and front lock

## Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Glass door provides attractive view of stored products

Factory-installed lock offers security you can count on

## Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished white cabinet	Allows the unit to be used freestanding
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Double pane tempered glass door	Heat resistant design provides clear view to promote impulse buys
Factory installed lock	Keyed lock for a secure interior
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Automatic defrost	Reduced user maintenance with automatic defrost
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

**SCR600LBITB Specifications:**

Overview	
Height	33.5"
Width	23.63"
Depth	23.6"
Depth with Handle	26.25"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	117.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.0"
Interior Width	20.75"
Interior Depth	17.5"
Compressor Step Height	6.0"

Compressor Step Width  
Compressor Step Depth

