

SWC525L7HVADA



32" x 19.38" x 22" (H x W x D)

Commercially listed ADA compliant 20" wide freestanding wine cellar with lock, digital thermostat and thin pro handle

Highlights:

ETL-S listed for commercial use

Slim 20" width is ideal for any setting

32" height complies with ADA guidelines

Glass door offers full display of interior

Product Features:

Slim 20" width	Full 4.5 cu.ft. capacity inside conveniently slim footprint
Commercially listed	ETL-S listed to NSF standards for commercial use
ADA compliant	32" high meets ADA guidelines
Fully finished black cabinet	Allows the unit to be used freestanding
Glass door	Provides a full display of stored contents
Factory installed lock	Keyed lock for secure interior
Professional handle	Thin 14mm diameter on vertical stainless steel handle
Automatic defrost	Reduced maintenance with auto defrost system
Digital thermostat	Electronic controls for precise temperature management, with indicator lights for red wine, white wine, and champagne temperatures



SWC525L7HVADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.56"
Width	19.38"
Depth	22.0"
Capacity	4.5 cu.ft.
Bottles	40 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.5
Voltage/Frequency	115 V AC/60 Hz
Weight	60.0 lbs.
Shipping Weight	83.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Shelf Type	Scalloped
Shelf Qty	6
Thermostat Type	Digital
Interior Light	Yes
Refrigerant Type	R134a
Refrigerant Amount	1.59 oz.
High Side PSI	218.0
Low Side PSI	105.0



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

✉ info@summitappliance.com



www.summitappliance.com