



# SWC525LADA



32" x 19.38" x 22" (H x W x D)

ADA compliant 20" wide freestanding wine cellar with lock and digital thermostat

### Highlights:

Slim 20" width is ideal for any setting

32" height complies with ADA guidelines

Digital thermostat lets you set the perfect temperature for reds, whites, or champagne

Factory installed lock provides security you can count on

### Product Features:

Slim 20" width	Full 4.5 cu.ft. capacity inside conveniently slim footprint
ADA compliant	32" high meets ADA guidelines
Fully finished black cabinet	Allows the unit to be used freestanding
Glass door	Provides a full display of stored contents
Factory installed lock	Keyed lock for secure interior
Automatic defrost	Reduced maintenance with auto defrost system
Digital thermostat	Electronic controls for precise temperature management, with indicator lights for red wine, white wine, and champagne temperatures
Scalloped shelves	Six adjustable chrome shelves are specially designed to hold wine bottles
Interior light	Turn the light on and off with a convenient rocker switch



## SWC525LADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.56"
Width	19.38"
Depth	22.0"
Capacity	4.5 cu.ft.
Bottles	40 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.5
Voltage/Frequency	115 V AC/60 Hz
Weight	57.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Scalloped
Shelf Qty	6
Thermostat Type	Digital
Interior Light	Yes
Refrigerant Type	R134a
Refrigerant Amount	1.59 oz.
High Side PSI	218.0
Low Side PSI	105.0



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

✉ info@summitappliance.com

🌐 www.summitappliance.com