



SWC525LCSS



33.25" x 19.38" x 22.25" (H x W x D)

20" wide wine cellar for built-in use, with stainless steel cabinet, lock, digital thermostat and towel bar handle

Highlights:

Flexible design allows built-in or freestanding use in 20" wide spaces

Glass door offers full display of interior

Digital thermostat lets you set the perfect temperature for reds, whites, or champagne

Factory installed lock provides security you can count on

Product Features:

Slim 20" width	Full 4.5 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished cabinet	Allows the unit to be used freestanding
Stainless steel wrapped cabinet	Durable 304 grade wrapping
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Factory installed lock	Keyed lock for secure interior
Automatic defrost	Reduced maintenance with auto defrost system
Digital thermostat	Electronic controls for precise temperature management, with indicator lights for red wine, white wine, and champagne temperatures
Scalloped shelves	Six adjustable chrome shelves are specially designed to hold wine bottles



SWC525LCSS Specifications:

Overview	
Height	33.25"
Width	19.38"
Depth	22.25"
Capacity	4.5 cu.ft.
Bottles	40 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.5
Voltage/Frequency	115 V AC/60 Hz
Weight	65.0 lbs.
Shipping Weight	95.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Shelf Type	Scalloped
Shelf Qty	6
Thermostat Type	Digital
Interior Light	Yes
Refrigerant Type	R134a
Refrigerant Amount	1.59 oz.
High Side PSI	218.0
Low Side PSI	105.0
Level Legs	2
Wheels	2



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

✉ info@summitappliance.com



www.summitappliance.com