

SWC6GBL



33.5" x 23.63" x 23.5" (H x W x D)

Commercially approved wine cellar for freestanding use with glass door, lock, and black cabinet

Highlights:

European built wine cellar designed for safe storage with elegant display

Commercially approved for use in foodservice establishments

Glass door offers full view of stored collection

Factory installed lock provides security you can count on



Product Features:

Commercially approved	ETL-S listed to NSF-7 for use in foodservice establishments
Slim counter height dimensions	Less than 24" wide to fit tight spaces
Fully finished black cabinet	Allows the unit to be used freestanding
Double pane tempered glass door	Display your collection behind a solid glass door trimmed in elegant brushed aluminum for a refined touch
Factory installed lock	Keyed lock for secure interior, conveniently located at the top of the door
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Automatic defrost	Reduced maintenance with auto defrost system
Scalloped steel shelving	Curved shelves designed for the ideal storage of wine bottles
Hidden evaporator	SUMMIT's original "hidden" evaporator is concealed in the wall so it never touches your fingers or food



SWC6GBL Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Capacity	5.5 cu.ft.
Bottles	36 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	115.0 lbs.
Shipping Weight	125.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Scalloped
Shelf Qty	4
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R134a
Refrigerant Amount	1.8 oz.
High Side PSI	285.0
Low Side PSI	70.0
Interior Height 1	26.0"
Interior Width 1	20.75"
Interior Depth 1	17.5"
Compressor Step Height	6.0"
Compressor Step Width	20.75"
Compressor Step Depth	5.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com



www.summitappliance.com