

SWC6GBLCSSADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant, commercially approved wine cellar for built-in undercounter use, with glass door and stainless steel cabinet

Highlights:

European built wine cellar designed for safe storage with elegant display

32" height fits under lower ADA compliant counters

Commercially approved and CalCode compliant

Fully wrapped stainless steel cabinet for modern elegance with solid durability

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Commercially approved	ETL-S listed to NSF-7 for use in foodservice establishments
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Stainless steel cabinet	Fully wrapped in stainless steel for lasting luxury
Double pane tempered glass door	Display your collection behind a solid glass door trimmed in elegant brushed aluminum for a refined touch
Factory installed lock	Keyed lock for secure interior, conveniently located at the top of the door
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Automatic defrost	Reduced maintenance with auto defrost system
Scalloped steel shelving	Curved shelves designed for the ideal storage of wine bottles



SWC6GBLCSSADA Specifications:

Overview	
Height	32.0"
Width	23.63"
Depth	23.5"
Capacity	5.5 cu.ft.
Bottles	36 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	125.0 lbs.
Shipping Weight	158.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Shelf Type	Scalloped
Shelf Qty	4
Thermostat Type	Dial
Interior Light	Yes
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8 oz.
High Side PSI	285.0
Low Side PSI	70.0
Interior Height 1	26.0"
Interior Width 1	20.75"
Interior Depth 1	17.5"
Compressor Step Height	6.0"
Compressor Step Width	20.75"

Compressor Step Depth



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com