

REFRIGERATOR MANUFACTURER
Turbo air
 more durable, efficient, beautiful

4184 E. Conant St.
 Long Beach, CA 90808
 Tel. 310-900-1000
 Fax. 310-900-1077
www.turboairinc.com

Project :	
Model # :	
Item # :	Qty :
Available W/H :	
Approval :	

Vertical Open Display Cases

Mid Heights
 Glass Side Panel / Solid Side Panel

Model : TOM-40M(B)



TOM-40MB



TOM-40MB-SP-A



TOM-40MB-SF

Stainless steel front panel
 available for all model (optional)
 * For the 'Stainless Steel Front (SF)' option,
 please allow 8-10 weeks lead time for shipping.



Self-cleaning condenser system

≡ FEATURES & BENEFITS ≡

- Modern design**
 By harmonizing curvature and rigidity, our modern style product designs are user-friendly while maintaining the highest product visibility and aesthetics.
- LED lighting interior display system**
 Brighter and longer lasting LED lights provide attractive, enhanced illumination compared to fluorescents. It saves energy by producing less heat, while maximizing the visibility in the display area.
- Self-cleaning condenser system**
 The accumulation of dust in the condenser causes the failure or breakdown of refrigerators. Refrigerators run normally until they reach a certain level of accumulation. At some point, when they are over the limit, their performance drops quickly resulting in damage to, or disposal of the stored products in refrigerators. The self-cleaning condenser system keeps the condenser clean and prevents system failure by automatically brushing daily.
- Solid side panels used to ensure durability (TOM-MB-SP(-A) models)**
- Interior materials available in two standards (TOM-MB-SP(-A) models)**
 Stainless steel interior for sanitary purposes or black coated interior with mirrored sides for maximized display effects.
- Environmentally friendly, efficient refrigeration system**
 Turbo Air's refrigerators are designed with oversized and balanced environmentally friendly R-404A (CFC Free) refrigeration. These include large evaporators and condensers for faster cooling and balanced temperature throughout the cabinet.
- Attractive, elegant, glass sided Euro design**
 Glass front shield and side walls optimize the merchandiser's display effects of fresh salads, sandwiches, desserts and beverages. Its elegant contemporary euro design will enhance any store application.
- Designed to enhance impulsive sales**
 Ideal for eye-catching displays and convenient access with fast service in high traffic area.
- Non-peel, durable anti-rust coating on the exterior reduces fingerprints**
- Standard back-guard improves airflow**
- Foamed with polyurethane, high-density cell insulation (CFC free)**
- 300 series stainless steel interior standard including back wall, shelves and deck pans**
- Perforated interior back wall and top for improved airflow**
- Front air intake and rear air discharge**



Model	CU./FT.	# of Shelves	HP	AMPS	Crated Weight (lbs.)	L x D x H (inches)
TOM-40M(B) TOM-40MB-SP(-A)	10.6	3	1	15	521	39 x 28 x 60 1/2

Vertical Open Display Cases

Mid Heights
Glass Side Panel / Solid Side Panel

Model : TOM-40M(B)

ELECTRICAL DATA	
Voltage	115/60/1
Plug Type	Ⓢ NEMA 5-20P
Full Load Amperes / LRA	15 / 77
Compressor HP	1
Refrigerant	R-404A
DIMENSIONAL DATA	
Net Capacity (cu. ft.)	10.6
Ext. Length Overall (in.)	39 (991mm)
Ext. Depth Overall (in.)	28 (711mm)
Ext. Height Overall (in.)	60 1/2 (1538mm)
Int. Length Overall (in.)	36 1/2 (927mm)
Int. Depth Overall (in.)	15 (381mm)
Int. Height Overall (in.)	33 7/8 (859mm)
Net Weight (lbs.)	421
Gross Weight (lbs.)	521
# of Shelves	3
Shelf Size (Top) (in.)	35 3/4 x 10 3/4
Shelf Size (Middle) (in.)	35 3/4 x 12
Shelf Size (Lower) (in.)	35 3/4 x 12

Design and specifications subject to change without notice.
Actual shipping weight may differ due to extra packing materials for product protection.

■ **WARRANTY : 2 Year Parts and Labor Warranty
Additional 3 Year Warranty on Compressor**

- **Simple plug-in installation**
- **Patented self-contained system, no plumbing required**
- **White and black color come standard**
- **Energy saving night curtain standard**
- **Recommended operating conditions**


TOM models are designed to operate in an environment where temperature & humidity do not exceed 75°F and 55% respectively. Units should not be installed near HVAC vents, fans or doorways that will disrupt the air curtain and compromise the function of the cabinet. Air curtain models will run most efficiently when completely loaded with product.

■ **OPTIONAL ACCESSORIES :**


- Stainless steel front panel
- Price tag channel

PLAN VIEW


(unit : inch)



TOP VIEW



FRONT VIEW



SIDE VIEW

(Interior)

Ver.201510



- Turbo Air : 800-627-0032
- GK : 800-500-3519
- Warranty : 800-381-7770
- AC : 888-900-1002

