






















CONTENTS


| REF. | QTY. | DESCRIPTION | REF. | QTY. | DESCRIPTION |
|------|------|------------------------------------|------|------|---|
| 1 | 1 | LEFT SIDE BACK PANEL | H1 | 22 | SHEET METAL  |
| 2 | 1 | RIGHT SIDE BACK PANEL | H2 | 4 | 6.5 PLAIN WASHER  |
| 3 | 1 | LEFT SIDE PANEL | H3 | 4 | 5.25 mm SPLIT WASHER  |
| 4 | 1 | RIGHT SIDE PANEL | H4 | 4 | M6 x 19 mm ROUND PHILLIP HEAD SCREW  |
| 5 | 1 | BOTTOM FRONT INNER SUPPORT CHANNEL | H5 | 6 | HINGE PIN  |
| 6 | 1 | BOTTOM FRONT KICK PLATE | H6 | 2 | BUMPER  |
| 7 | 1 | BOTTOM SHELF | H7 | 12 | PLASTIC HINGE CAP  |
| 8 | 1 | TOP SHELF | H8 | 16 | SHELF CLIP  |
| 9 | 4 | GUSSET REINFORCEMENT PLATE | H9 | 6 | PLASTIC INSERT  |
| 10 | 1 | LEFT DOOR | H10 | 1 | RIGHT HAND DOOR HANDLE  |
| 11 | 1 | RIGHT DOOR | H11 | 2 | BACK PLATE  |
| 12 | 4 | SHELF | H12 | 4 | 5.5mm SPLIT WASHER  |
| | | | H13 | 4 | M5 x 8mm ROUND PHILLIP HEAD SCREW  |
| | | | H14 | 1 | COTTER PIN  |
| | | | H15 | 1 | LOCK LATCH  |
| | | | H16 | 2 | LOCKING ROD  |
| | | | H17 | 1 | LOCKING BRACKET  |
| | | | H18 | 1 | LEFT HAND DOOR HANDLE  |
| | | | H19 | 2 | ROD GUIDE  |
| | | | | 2 | KEY  |




WARNING.

1. USE 2 PEOPLE TO ASSEMBLE.
2. LAY PARTS ON SOFT SMOOTH NON-SCRATCH SURFACE.
3. DO NOT OVERLOAD SHELVES.
4. LOAD LOWER SHELVES FIRST.
5. DO NOT CLIMB OR STAND ON SHELVES.







H

10

SHELF

SEE DETAIL H and I

H8

I

11

SEE LOCK ASSEMBLY DETAILS.


H13

H12


H11

H18






H9



LOCK ASSEMBLY



RIGHT DOOR ROD
ASSEMBLY



BEND 1 LEG OF
COTTER PIN WITH PLIERS.