

Ultrasonic Cool Mist Humidifier



#CZHD81 (125151)

- Digital Control Panel for Adjustable Mist Intensity & Timer
- Adjustable 360° Dual Mist Vents
- Up to 20 Hours of Operation
- Low Power Consumption
- Whisper-Quiet Operation
- Auto Shut-Off with Indicator Light and Tone for Empty Tank
- Filter-Free Design
- Anti-Microbial Treated Polymer Plastic
- ETL Approved for Sale in the US and Canada




Product Specifications

Humidifier Type	Ultrasonic Cool Mist
Voltage	120 VC, 60 Hz
Watts	
Tank Capacity	1.1 Gallon (4.16 Liters)
Mist Output	0.2 Liters/hour
Max Run Time	20 hours

Item Dimensions	L- 7.0" x W- 7.0" x H- 12.5"
Box Dimensions	L- 8.4" x W- 8.4" x H- 13.4"
Box Cube	0.55'
Box Weight	4.04 lbs.
Item UPC	075877011510

MS Dimensions	L- 26.0" x W- 17.5" x H- 14.0"
MS Case Qty	6
MS Cube	3.69"
MS Weight	24.25 lbs.
MS 12of5 UPC	20075877011514



Pallet Qty	90
40' HQ Qty	3,780
Port	Ningbo



Medium Room



www.comfortzone-us.com

Tel: 800-523-1268
609-860-9990
Fax: 609-860-9991
324A Half Acre Rd.
Cranbury, NJ 08512

