

## Electric Heaters

**Model P4000**

**Model P6000**



**CLEAN  
DRY  
HEAT!**




**100°F  
Temperature  
Rise**



- Built-in thermostat (32° - 100° F)
- Ductable to 50'
- Overheat protection
- Three power settings

### SPECIFICATIONS

	P4000 	P6000
Input BTU/Kw	136,000 / 40	204,700 / 60
	109,200 / 32	163,800 / 48
	54,600 / 16	81,900 / 24
Electrical Rating	480 Volts / 3Ø / 50 amps	480 Volts / 3Ø / 75 amps
Fan	1800 CFM	1800 CFM
Temperature Rise	100°F	100°F
Dimensions	46"L x 20"W x 25"H	46"L x 20"W x 25"H
Approx. Weight	130 lbs.	158 lbs.

