

# Electric Heater

**Model  
P600  
P900**



**CLEAN  
DRY  
HEAT!**



**Includes Pigtail  
and Plug**



**100°F  
Temperature  
Rise**

- **Built-in thermostat (32° - 100° F)**
- **Overheat protection**
- **High quality sealed motor**
- **Stainless steel jacketed coils**
- **High quality sealed motor**
- **Installed with 10' cord and grounded plug**

## SPECIFICATIONS

<b>Model:</b>	<b>P600</b>	<b>P900</b>
Input BTU/Kw	20,500 / 6	30,700 / 9
Electrical Rating	240 Volts / 1Ø / 25 amps	240 Volts / 1Ø / 38 amps
Power Cord	10', SO Type, 8-3	10', SO Type, 8-3
Grounded Plug	NEMA 14-30	NEMA 14-50
Fan	250 CFM	350 CFM
Temperature Rise	100°F	100°F
Dimensions	19.5"L x 11.8"W x 17.3"H	22"L x 18"W x 12"H
Approx. Weight	33 lbs.	48 lbs.



342 N. 400 E. Valparaiso, IN 46383  
219-464-8818 • 219-462-7985 • [www.heatwagon.com](http://www.heatwagon.com)