

DUAL READOUT THERMOMETER



Makes Calculations Easier

The industry's only manifold-compatible compact thermometer with two readings to help simplify the calculation of superheat and subcool.



Superior Versatility

Use it on any gauge set, or remove it and use it independently.



Reads Temperatures Quickly

Two easy-to-use, K-style tube-clamp thermocouples get you to the temperature reading quickly.



This thermometer is the first in the industry to attach to any manifold.

Product Specifications

Item Number	1839106		
Product Description	DROT2TCC		
Two Thermocouples Included	1839108 TCC Thermocouple Clamp		
Batteries	AA x 1 (included)		
Battery Life	151 hours		
Connection Type	K		
Measurement	Range	Resolution	Accuracy
Temperature	-76°F to 999.9°F	.10° F/C	±2.0 C°/±3.6°F

Operating Temperature Range 0°C to +50°C (LCD)

Dimensions	
Length	1-3/4"
Width	1-5/8"
Height	3-7/8"
Weight	11 oz.



Scan this QR Code to watch the Dual Readout Thermometer in action.



Dual Readout Thermometer
1839106