

THERMOCOUPLE CLAMP

Get right to it on up to 1-1/8" tubing with hilmor's Thermocouple Clamp. A K-style connection offers a secure fit and is easy to use with other devices. It is a perfect pairing for the hilmor Dual Readout Thermometer. When the job is done, it is easy to stow it away. Simply wrap the thermocouple wire around the handle, and secure the plug into the clamp.



Fast, Precise Readings

Gets right to the temperature reading up to 1-1/8" tubing.



Secure Connection

K-style connection provides a tight fit and easy use with other devices.



Secure Storage

Stow it away simply by wrapping the thermocouple wire around the clamp and securing the plug.



Protect the thermocouple plug when not in use by wrapping the cord around the handle and plugging into the side socket.

Product Specifications

Item Number	1839108
Product Description	TCC
Connection Type	K
Accuracy	+/-2.0°C/+/-3.6°F
Operating Temperature (plastic)	-40°F to 250°F

Dimensions

Length	5-1/4"
Width	7/8"
Height	3-1/4"
Weight	3 oz.



Attach K-style clamp to an easily accessible spot on the hilmor manifold.



K-style clamp securely attaches to tubing up to 1-1/8" for measurements on the double.



Thermocouple Clamp
1839108