

REFRIGERATION HOSES

hilmor 36" and 60" Hoses are designed with smart features including an extra abrasion-resistant layer for tough environments.



Superior Protection

An extra abrasion-resistant layer for the tough environments of HVAC/R.



Handles High Pressure

Rated for 800 PSI working pressure to work with high-pressure refrigerants.



36" Vacuum Hose
1839159



Product Specifications

60" Hoses

| Item Numbers | Product Descriptions | Diameter |
|--------------|---------------------------|----------|
| 1839150 | H60R Hose 60" - Red | 1/4" |
| 1839151 | H60B Hose 60" - Blue | 1/4" |
| 1839152 | H60Y Hose 60" - Yellow | 1/4" |
| 1839153 | H60S3 Hose 60" - Set of 3 | 1/4" |
| 1839154 | H6038 Hose 60" - VAC | 3/8" |

Maximum Allowable Working Pressure

800 PSI

Burst Pressure

4000 PSI

Operating Temperature

-20°F to +180°F

End Connection

Straight by 45 degree

Dimensions

Length

60"

Weight

8 oz.

36" Hoses

| Item Numbers | Product Descriptions | Diameter |
|--------------|---------------------------|----------|
| 1839155 | H36R Hose 36" - Red | 1/4" |
| 1839156 | H36B Hose 36" - Blue | 1/4" |
| 1839157 | H36Y Hose 36" - Yellow | 1/4" |
| 1839158 | H36S3 Hose 36" - Set of 3 | 1/4" |
| 1839159 | H3638 Hose 36" - VAC | 3/8" |

Maximum Allowable Working Pressure

800 PSI

Burst Pressure

4000 PSI

Operating Temperature

-20°F to +180°F

End Connection

Straight by 45 degree

Dimensions

Length

36"

Weight

6 oz.

Replacement Parts

| Category | Item Numbers | Product Descriptions | Location # |
|----------|--------------|---|------------|
| Hoses | 1932984 | HGL Hose Gaskets (3/8", Pack of 10) | 1 |
| Hoses | 1932982 | HGS Hose Gaskets (1/4", Pack of 12) | 2 |
| Hoses | 1932985 | HTD Hose Threaded Depressors, Pack of 6 | 3 |