




## POWER & EFFICIENCY

INPUT POWER OPTIONS	AC 1PH 200-240V 50/60Hz   AC 3PH 200-240V 50/60Hz   AC 3PH 380-480V 50/60Hz		
CURRENT AT MAX SPEED (Amp)	4.6-3.8 A		2.4 - 2.0 A   1.8 - 1.7 A
POWER (hp)	5/8 HP		
MAXIMUM SPEED (RPM)	107 RPM		
MAX AFFECTED AREA	60 ft Dia   3,600 sqft		

## DIMENSIONS & WEIGHT

FAN DIAMETER	12 ft
FAN WEIGHT	101 lbs (46 kg)



Pictured with 2 ft downrod

## MOUNTING & SAFETY

MOUNTING OPTIONS	I-beam   Glulam
DOWNROD (A)	Downrods available in 1 ft increments: 2 ft min., 10 ft max. Downrod length must be specified at time of order.
SAFETY FEATURES	Fan Retention System   Airfoil Retention System   Fire relay

## IN THE BOX

INCLUDED	Fan I-beam mount with pre-wired downrod   Control panel   Install manual Wall Control   Mounting hardware kit   Communication Kit   Guy wire kit
OPTIONAL	Additional cable lengths   Network Controller   Glulam brackets

## WARRANTY & CERTIFICATIONS

CERTIFICATIONS	ETL/Intertek-certified to ANSI/UL 507 and CSA C22.2 No. 113 in North America
WARRANTY <sup>1</sup>	10-year, Non-Prorated Warranty

<sup>1</sup>See complete warranty for details.