




## POWER & EFFICIENCY

INPUT POWER OPTIONS	AC 1PH 200-240V 50/60Hz   AC 3PH 200-240V 50/60Hz   AC 3PH 380-480V 50/60Hz		
CURRENT AT MAX SPEED (Amp)	6.3 - 5.6 A		2.6 - 2.1 A   2.3 - 1.8 A
POWER (hp)	5/8 HP		
MAXIMUM SPEED (RPM)	61 RPM		
MAX AFFECTED AREA	120 ft Dia   14,400 sqft		

## DIMENSIONS & WEIGHT

FAN DIAMETER	24 ft
FAN WEIGHT	159 lbs (72 kg)



Pictured with 2 ft downrod

## MOUNTING & SAFETY

MOUNTING OPTIONS	I-beam   Glulam
DOWNROD (A)	Downrods available in 1 ft increments: 2 ft min., 10 ft max. Downrod length must be specified at time of order.
SAFETY FEATURES	Fan Retention System   Airfoil Retention System   Fire relay

## IN THE BOX

INCLUDED	Fan I-beam mount with pre-wired downrod   Control panel   Install manual Wall Control   Mounting hardware kit   Communication Kit   Guy wire kit
OPTIONAL	Additional cable lengths   Network Controller   Glulam brackets

## WARRANTY & CERTIFICATIONS

CERTIFICATIONS	ETL/Intertek-certified to ANSI/UL 507 and CSA C22.2 No. 113 in North America
WARRANTY <sup>1</sup>	10-year, Non-Prorated Warranty

<sup>1</sup>See complete warranty for details.