

# ESN-40 ELECTRIC SCHEDULE 40 PIPE NOTCHER

754420

The JET Electric Pipe Notcher provides fast and clean 90° notches in schedule 40 pipes to maximize productivity. The 220-volt single-phase machine is designed to for durability and ease of operation.



## FEATURES

- Designed to Notch Schedule 40 Pipe all day long
- CSA/US: Following strict guidelines and electrical requirements, this JET Notcher is CSA/US certified
- Magnetic Switch for Low Voltage Motor Protection
- Safety Guarding surrounding all notching dies
- Insert the end of the pipe, notch one side, rotate pipe 180°, reinsert to notch the other side
- Replacement dies available in wide range of sizes
- Benchtop mounting fits on almost any bench in your shop



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# ESN-40 ELECTRIC SCHEDULE 40 PIPE NOTCHER

754420

## SPECIFICATIONS

Notch Capacity	1/4, 3/8, 1/2, 3/4, 1, 1-1/4, 1-1/2, 2
Overall Dimensions (L x W xH) (In.)	33-15/32 x 17-23/32 x 18-57/64
Notching	90° Fixed Angle
Weight (Lbs.)	249
Motor (HP)	2 HP, 220V, 1-Ph
Max. Wall Thickness (In.)	1/8



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE