

# LF-20 20GA PITTSBURGH LOCKFORMER

756090

The JET Lockformer is all about durability. The all steel forming head, case hardened steel forming rolls and needle nose roller bearings contribute to years of precision performance. The heavy-duty undercarriage helps prevent damage during forklift transportation.



## FEATURES

- All steel forming head with hardened and ground shafts
- Case hardened steel forming rolls, machine cut gear for long use
- Needle nose roller bearings for years of precision use
- Reinforced undercarriage for damage free lifting with a fork lift
- CSA/US: Following strict guidelines and electrical requirements, this JET Lockformer is CSA/US certified
- Magnetic Switch for motor protection
- Tool less roller cover panel for easy access
- Onboard tool storage tray



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# LF-20 20GA PITTSBURGH LOCKFORMER

756090

## SPECIFICATIONS

|                                     |                      |
|-------------------------------------|----------------------|
| Mild Steel Capacity (Gauge)         | 20                   |
| Overall Dimension (L x W x H) (In.) | 36 x 16-1/2 x 36-1/2 |
| Speed (FPM)                         | 25                   |
| Weight (Lbs.)                       | 340.84               |
| Width of Hammer Over Edge (Adj.)    | 5/16 to 3/8          |



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE