

GHB-1340A WITH NEWALL DP700 DRO WITH TAPER ATTACHMENT AND COLLET CLOSER

321104

JET geared head bench lathes feature an enclosed gearbox for smooth, quiet operation. Precision roller bearings support the hardened and ground spindle resulting in tight tolerances. Each JET Lathe comes loaded with features you've come to expect, all backed by the industry leading JET Two Year Warranty.



FEATURES

- One of the most popular JET lathes now comes with an enclosed gearbox as a standard feature
- Enclosed gearbox design provides smooth, quiet operation
- Fast, easy speed changes
- Hardened and ground gears are featured in the headstock and gearbox
- D1-4 Spindle is precision ground for accuracy and supported by high quality tapered roller bearings
- Headstock is constantly oiled during operation
- Gear box gives wide inch threading and feed capabilities with no gear changes
- V-way bed design is induction hardened and ground
- Gap bed section provided for larger diameter work
- Independent leadscrew and feed rod
- Spindle actuation control is apron mounted
- Compound and cross slide have backlash elimination
- Adjustable gibs are incorporated in the carriage and slideways
- Tailstock may be offset for turning tapers and includes an inch-metric graduated quill
- Oil pan included
- Tolerance test certificate included
- 6" 3-jaw direct mount chuck with top reversing jaw
- 8" 4-jaw chuck
- 12" face plate
- Steady and follow rest
- Four-way tool post
- Metric change gear
- Splash guard
- Centers and headstock center sleeve
- Threading dial
- Tool box and tools



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

GHB-1340A WITH NEWALL DP700 DRO WITH TAPER ATTACHMENT AND COLLET CLOSER

321104

SPECIFICATIONS

| | |
|---|------------------|
| Size | 13 x 40 |
| Digital Readout | Newall DP700 |
| Accessory 1 | Taper Attachment |
| Accessory 2 | Collet Closer |
| Swing Over Bed (In.) | 13 |
| Swing Over Cross Slide (In.) | 7-25/32 |
| Swing Through Gap (In.) | 18-3/4 |
| Length of Gap (In.) | 8 |
| Distance Between Centers (In.) | 43 |
| Spindle Bore (In.) | 1-3/8 |
| Spindle Mount | D1-4 |
| Spindle Taper with Sleeve | MT-5 (MT-3) |
| Number of Spindle Speeds | 8 |
| Range of Spindle Speeds (RPM) | 70 - 2,000 |
| Number of Longitudinal and Cross Feed Rates | 40 |
| Range of Longitudinal Feeds (IPR) | .0018 - .0374 |
| Range of Cross Feeds (IPR) | .0006 - .0130 |



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

GHB-1340A WITH NEWALL DP700 DRO WITH TAPER ATTACHMENT AND COLLET CLOSER

321104

FULL SERIES

| STOCK NO | MODEL NO | SIZE | DIGITAL READOUT | ACCESSORY 1 | ACCESSORY 2 | ACCESSORIES |
|----------|-----------|---------|-----------------|------------------|---------------|-------------|
| 321357A | GHB-1340A | 13 x 40 | | | | |
| 321101AK | GHB-1340A | 13 x 40 | | | | Stand |
| 321119 | GHB-1340A | 13 x 40 | | Taper Attachment | | |
| 321124 | GHB-1340A | 13 x 40 | | | Collet Closer | |
| 321129 | GHB-1340A | 13 x 40 | | Taper Attachment | Collet Closer | |
| 321103 | GHB-1340A | 13 x 40 | ACU-RITE VUE | | | |
| 321103AK | GHB-1340A | 13 x 40 | ACU-RITE VUE | | | Stand |
| 321102 | GHB-1340A | 13 x 40 | ACU-RITE VUE | | Collet Closer | |
| 321226 | GHB-1340A | 13 x 40 | ACU-RITE VUE | Taper Attachment | Collet Closer | |
| 321122 | GHB-1340A | 13 x 40 | ACU-RITE 200S | | | |
| 321123 | GHB-1340A | 13 x 40 | ACU-RITE 200S | Taper Attachment | | |
| 321125 | GHB-1340A | 13 x 40 | ACU-RITE 200S | | Collet Closer | |
| 321127 | GHB-1340A | 13 x 40 | ACU-RITE 200S | Taper Attachment | Collet Closer | |
| 321131 | GHB-1340A | 13 x 40 | Newall DP700 | | | |
| 321115 | GHB-1340A | 13 x 40 | Newall DP700 | Taper Attachment | | |
| 321581 | GHB-1340A | 13 x 40 | Newall DP700 | | Collet Closer | |
| 321104 | GHB-1340A | 13 x 40 | Newall DP700 | Taper Attachment | Collet Closer | |

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE