

AP1-M, 1-TON ARBOR PRESS

333610

Every JET arbor press is made of a heavy ductile iron casting that offers incredible strength and rigidity to the overall framework. The base, ram housing, framework and 4 position bottom plate are precision machined for unquestioned accuracy.



FEATURES

- ARBOR PRESSES
- For all production and assembly applications
- Precision cut steel rams and pinions for accurate operation
- Tables and slotted table-plates are flat and parallel to provide accurate support



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

AP1-M, 1-TON ARBOR PRESS

333610

SPECIFICATIONS

Capacity (Tons)	1
Max. Work Height (In.)	5-1/8
Overall Dimensions (L x W xH) (In.)	9-1/2 x 7-1/2 x 12
Weight (Lbs.)	27
Capacity Over Table (In.)	5
Anvil Diameter (In.)	3-1/2
Size of Ram (In.)	1 x 9-1/8
Diameter of Work (In.)	8
Arbor Press Height (In.)	12
Base Size (In.)	5 x 9-1/2
Ram Bore (In.)	1/2
Travel of Ram (In.)	5-4/5
Approx. Pressure (Tons)	1



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE