

J-2350, 28" 3HP DIRECT DRIVE DRILL PRESS

354050

Shops must handle a wide variety of customer demands. This heavy-duty JET machine performs a variety of precision drilling applications. An easy-to-ready internal depth gauge prevents waste through errors, and a large production with T-slotted base holds over-sized pieces.



FEATURES

- Tempered, ground spindle with internal taper mounted in precision bearings for maximum accuracy, minimizing deflection
- Speed and feed selectors are located on one side of the drill head for convenience and ease of operation
- Oversized base is precision ground with T-slot for added versatility and stability
- Mechanical powerfeed clutch engagement
- Two-speed forward and reverse switch
- Automatic tool ejector
- Heavy-duty quill
- Low voltage controls
- Manual quill lock
- Coolant system
- Does NOT perform Tapping function



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-2350, 28" 3HP DIRECT DRIVE DRILL PRESS

354050

SPECIFICATIONS

Style (Type)	Direct Drive
Drills to Center of Circle (In.)	28
Drilling Capacity Cast Iron (In.)	1-7/8
Drilling Capacity Mild Steel (In.)	1-3/4
Column Diameter (In.)	6-7/8
Distance Column to Spindle (In.)	14
Range of Spindle Speeds (RPM)	82, 120, 180, 240, 354, 528, 678, 1026, 1,524
Spindle Taper (In. x TPI)	MT-4
Spindle Travel (In.)	9
Spindle Distance to Base (In.)	49
Spindle Distance to Table (Max.) (In.)	30-1/2
Table Size (L x W) (In.)	22 x 19
T-Slots Number and Size (In.)	3 - 5/8
Work Table Weight Capacity (Lbs.)	400
Base Dimensions (In.)	40 x 30
Base Slots Number & Size (In.)	3 x 5/8
Motor (HP)	3 HP, 230/460V, 3Ph



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE