

# J-2500, 15" FLOOR MODEL DRILL PRESS 115V 1PH

354400

Accuracy, stability and versatility are the benchmark features of the JET 15" and 20" Drill Presses. This high quality line of JET Drill Presses offer a greater range in spindle speeds than other machines of this class. JET backs their machines with the industry-leading Two Year Warranty.



## FEATURES

- Constructed to provide a solid base for drilling
- The enclosed spindle assembly is supported by four permanently lubricated ball bearings for greater precision and accuracy
- Cast Iron head
- Large ground steel column for maximum head and table support
- Large quill allows greater accuracy
- 3-1/8" stroke for deep hole applications
- Accurate depth stop for precise hole depths
- Table tilts 45°
- 5/8" drill chuck and arbor
- Telescoping safety spindle guard



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-2500, 15" FLOOR MODEL DRILL PRESS 115V 1PH

354400

## SPECIFICATIONS

Style (Type)	Belt Drive
Drills to Center of Circle (in.)	15
Drilling Capacity Cast Iron (In.)	5/8
Drilling Capacity Mild Steel (In.)	1/2
Distance Column to Spindle (In.)	7-1/2
Number of Spindle Speeds	16
Range of Spindle Speeds (RPM)	200, 290, 350, 430, 500, 580, 640, 720, 800, 870, 1,440, 1,630, 1,820, 2,380, 2,540, 3,630
Column Diameter (In.)	2-7/8
Spindle Taper (In. x TPI)	MT-2
Spindle Travel (In.)	3-3/8
Spindle Distance to Base (In.)	48
Spindle Distance to Table (Max.) (In.)	24
Table Size (L x W) (In.)	11-1/2 x 11-1/2
Table Travel (In.)	24
T-Slots Number and Size (In.)	-
T-Slot Centers (In.)	-
Work Table Weight Capacity (Lbs.)	44



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE