

# J-FK350-4K, 350MM FERROUS MANUAL COLD SAW

414217K

JET Coldsaws deliver clean, burr-free cuts and offer machine shop and fabrication professionals a list of features and standard design characteristics that you've come to expect from JET. All backed by the industry leading full service Two Year Warranty



## FEATURES

- 350mm (14") Ferrous Cold Saw for steel, stainless and tough to cut alloys.
- Spring loaded whole hand trigger starts or stops the sawing process for easy smooth cutting and increased user safety
- Quick tension and release mitering capabilities with stops at 45° right, 45° left, and 90° (center), capable of slotting
- Two-piece cast iron blade guard system permits quick and easy blade changes without removing the guards
- Hardened and ground worm screw and wheel drive gear box operates in an oil bath for added durability
- Double self centering vise with adjustable gibs secures the material for burr free cuts
- Heavy-Duty cast iron frame base with easy access storage provides a stable cutting platform
- Thermal overload protection with magnetic starter for increased electrical safety
- Flood style coolant with flow control system extends blade life
- 30" adjustable length material stop



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-FK350-4K, 350MM FERROUS MANUAL COLD SAW

414217K

## SPECIFICATIONS

Style (Type)	Ferrous
Blade Speeds (RPM)	44, 88
Tubing Round at 90 Degrees (In.)	4-1/2
Tubing Round at 45 Degrees (In.)	3-1/2
Tubing Square at 90 Degrees (In.)	4-19/64 x 4-19/64
Tubing Square at 45 Degrees (In.)	3-19/64 x 3-19/64
Tubing Rectangle at 90 Degrees (In.)	5-1/2 x 3-57/64
Tubing Rectangle at 45 Degrees (In.)	3-19/64 x 3
Solid Round at 90 Degrees (In.)	3
Solid Round at 45 Degrees (In.)	2-25/64
Solid Square at 90 Degrees (In.)	3 x 3
Solid Square at 45 Degrees (In.)	2-25/64 x 2-25/64
Blade Size (Mm.)	350 x 32 x 2-1/2
Maximum Vise Opening (In.)	6
Motor (HP)	2 HP, 440V, 3Ph
Overall Dimensions (L x W xH) (In.)	50 x 28 x 60
Weight (Lbs.)	794



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-FK350-4K, 350MM FERROUS MANUAL COLD SAW

414217K

## FULL SERIES

STOCK NO	MODEL NO	STYLE (TYPE)	BLADE SPEEDS (RPM)	CUTTING CAPACITY TUBING (IN.)	TUBING ROUND AT 90 DEGREES (IN.)	TUBING ROUND AT 45 DEGREES (IN.)
414214K	J-FK350-2K	Ferrous	44, 88		4-1/2	3-1/2
414217K	J-FK350-4K	Ferrous	44, 88		4-1/2	3-1/2
414227	CS-315	Ferrous	52, 104		3-1/2	3-1/2
414229	CS-315-1	Ferrous	54		3-1/2	3-1/2
414226	CS-275	Ferrous	54, 108		3-19/64	3-19/64
414228	CS-275-1	Ferrous	54		3-19/64	3-19/64
414220	J-F225	Ferrous	52		2-1/2	2

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE