

J-F225, 225MM FERROUS MANUAL BENCH COLD SAW

414220

The table-top J-F225 enables one to take JET power and precision wherever the job requires. Adjustable depth stop, safety spring loaded trigger switch in the handle and manual vise combine to give this JET saw precision and reliability professionals demand from their machines. Features you've come to expect, backed by the industry-leading JET Two Year Warranty



FEATURES

- 225mm (9") Ferrous Cold Saw for steel, stainless and tough to cut alloys.
- Hardened and ground worm screw with a bronze drive gear operating in an oil bath increases dependability and reliability
- The double self centering vise secures the material on both sides of the cut for added sawing precision and burr free cuts
- Control handle with a safety spring loaded trigger switch to start or stop the machine increases user safety
- Large liquid reservoir and pump in the base keeps the blade flooded with coolant, extending blade life.
- Fully adjustable material depth stop for sawing repeatability and increased production
- Saw head manually miters to 45° to the left
- 225mm (9") blade included



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-F225, 225MM FERROUS MANUAL BENCH COLD SAW

414220

SPECIFICATIONS

Style (Type)	Ferrous
Blade Speeds (RPM)	52
Tubing Round at 90 Degrees (In.)	2-1/2
Tubing Round at 45 Degrees (In.)	2
Tubing Square at 90 Degrees (In.)	2-1/4 x 2-1/4
Tubing Square at 45 Degrees (In.)	1-5/8 x 1-5/8
Tubing Rectangle at 90 Degrees (In.)	2-1/2 x 2-15/16
Tubing Rectangle at 45 Degrees (In.)	1-3/4 x 1-1/4
Solid Round at 90 Degrees (In.)	2-1/2
Solid Round at 45 Degrees (In.)	2
Solid Square at 90 Degrees (In.)	2-1/4 x 2-1/4
Solid Square at 45 Degrees (In.)	1-5/8 x 1-5/8
Solid Rectangle at 90 Degrees (In.)	2-1/2 x 2-15/16
Solid Rectangle at 45 Degrees (In.)	1-3/4 x 1-1/4
Blade Size (Mm.)	225 x 32 x 2
Maximum Vise Opening (In.)	6
Motor (HP)	1 HP, 115V, 1Ph



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-F225, 225MM FERROUS MANUAL BENCH COLD SAW

414220

FULL SERIES

STOCK NO	MODEL NO	STYLE (TYPE)	BLADE SPEEDS (RPM)	CUTTING CAPACITY TUBING (IN.)	TUBING ROUND AT 90 DEGREES (IN.)	TUBING ROUND AT 45 DEGREES (IN.)
414214K	J-FK350-2K	Ferrous	44, 88		4-1/2	3-1/2
414217K	J-FK350-4K	Ferrous	44, 88		4-1/2	3-1/2
414227	CS-315	Ferrous	52, 104		3-1/2	3-1/2
414229	CS-315-1	Ferrous	54		3-1/2	3-1/2
414226	CS-275	Ferrous	54, 108		3-19/64	3-19/64
414228	CS-275-1	Ferrous	54		3-19/64	3-19/64
414220	J-F225	Ferrous	52		2-1/2	2

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE