

CS-315, 315MM FERROUS MANUAL COLD SAW

414227

JET Coldsaws deliver clean, burr-free cuts and offer machine shop and fabrication professionals a list of features and standard design characteristics that you've come to expect from JET. All backed by the industry leading full service Two Year Warranty



FEATURES

- Now available in Single Phase 230V
- Two-piece cast iron blade guard system permits quick and easy blade changes without removing the guards
- Quick clamping cam-action vise with adjustable gib and material support bar for burr-free cutting operations
- Hardened and ground direct drive worm shaft and bronze worm wheel transmits maximum torque to the saw blade
- Blade drive reduction gearbox operates in an oil bath for increased durability
- Heavy-Duty cast iron frame base with easy access storage provides a stable cutting platform
- 1-1/3 Gallon coolant reservoir and pump with flow control system extends blade life
- Quick tension and release mitering capabilities with stops at 45° right, 45° left
- Fully adjustable material depth stop for sawing repeatability and increased production



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

CS-315, 315MM FERROUS MANUAL COLD SAW

414227

SPECIFICATIONS

Style (Type)	Ferrous
Blade Speeds (RPM)	52, 104
Tubing Round at 90 Degrees (In.)	3-1/2
Tubing Round at 45 Degrees (In.)	3-1/2
Tubing Square at 90 Degrees (In.)	3-3/16 x 3-3/16
Tubing Square at 45 Degrees (In.)	2-19/32 x 2-19/32
Tubing Rectangle at 90 Degrees (In.)	4 x 3-3/16
Tubing Rectangle at 45 Degrees (In.)	3-3/16 x 2-19/32
Solid Round at 90 Degrees (In.)	3-1/2
Solid Round at 45 Degrees (In.)	3-1/2
Solid Square at 90 Degrees (In.)	3-1/8 x 3-1/8
Solid Square at 45 Degrees (In.)	2-19/32 x 2-19/32
Solid Rectangle at 90 Degrees (In.)	3-3/16 x 3-3/16
Solid Rectangle at 45 Degrees (In.)	3-3/16 x 2-19/32
Blade Size (Mm.)	315 x 32 x 2
Maximum Vise Opening (In.)	4-11/16
Motor (HP)	2 HP, 230V, 3Ph



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

CS-315, 315MM FERROUS MANUAL COLD SAW

414227

FULL SERIES

STOCK NO	MODEL NO	STYLE (TYPE)	BLADE SPEEDS (RPM)	CUTTING CAPACITY TUBING (IN.)	TUBING ROUND AT 90 DEGREES (IN.)	TUBING ROUND AT 45 DEGREES (IN.)
414214K	J-FK350-2K	Ferrous	44, 88		4-1/2	3-1/2
414217K	J-FK350-4K	Ferrous	44, 88		4-1/2	3-1/2
414227	CS-315	Ferrous	52, 104		3-1/2	3-1/2
414229	CS-315-1	Ferrous	54		3-1/2	3-1/2
414226	CS-275	Ferrous	54, 108		3-19/64	3-19/64
414228	CS-275-1	Ferrous	54		3-19/64	3-19/64
414220	J-F225	Ferrous	52		2-1/2	2

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE