

# HBS-56S, 5" X 6" HORIZONTAL MITERING BANDSAW

414457

JET Mitering Horizontal bandsaws unique design features a swiveling head while the base remains stationary. This allows the stock to remain same position while making accurate crosscuts and miters. Backed by the industry leading two year warranty, JET Mitering Bandsaws are built to last and deliver precision results.



## FEATURES

- For added safety, the HVBS-56S follows strict guidelines and electrical requirements to be certified by CSA Group
- Blade drive is a sealed, steel, heat treated worm driving a bronze worm gear in an oil bath
- Mitering head swivels to cut any angle 0° - 60° while the work piece remains secured
- Ball bearing supported blade wheel
- Fully adjustable hydraulic downfeed system
- Deluxe enclosed stand with wheels and handle for easy movement
- Adjustable material stop
- 1/2" Carbon Steel Blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# HBS-56S, 5" X 6" HORIZONTAL MITERING BANDSAW

414457

## SPECIFICATIONS

Cutting Capacity (W x D) (In.)	5 x 6
Round at 90 Degrees (In.)	5
Round at 45 Degrees (In.)	3
Rectangle at 90 Degrees (In.)	5 x 6 and 2 x 6-3/4
Rectangle at 45 Degrees (In.)	4 x 2-3/4 and 2 x 3-3/4
Vise Swivels (Deg.)	45°
Head Movement (Deg.)	60°
Blade Size (In.)	1/2 x .025 x 64-1/2
Blade Length (In.)	64-1/2
Blade Wheel Diameter (In.)	7-3/8
Blade Speed (SFPM)	80, 120, 200
Bed Height (In.)	28
Motor (HP)	1/2 HP, 115/230V, 1Ph
Drive	Belt Drive
Overall Dimensions (L x W x H) (In.)	37 x 20-3/4 x 41
Weight (Lbs.)	172



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE