

# HBS-814GH, 8" X 14" HORIZONTAL GEARED HEAD BANDSAW

414466

The JET HBS-814GH was engineered with the operator in mind. An easy access control panel and heavy-duty geared head transmission for quick speed change means productivity never slows. Like every JET machine we manufacture, professionals know they can rely on this saw when the project is on the line.



## FEATURES

- Hardened and ground drive shaft and worm gears transmit maximum torque to blade wheels
- Heavy-duty geared head transmission for quick speed changes
- Fully adjustable hydraulic downfeed system
- Easily accessible saw control panel
- Quick-positioning vise with fully adjustable jaws, swivels to 45°
- Built-in, self propelled blade brush extends blade life
- Wheels permit easy storage and movement
- Coolant system
- Adjustable material stop
- 3/4" Bi-Metal blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# HBS-814GH, 8" X 14" HORIZONTAL GEARED HEAD BANDSAW

414466

## SPECIFICATIONS

Cutting Capacity (W x D) (In.)	8 x 14
Round at 90 Degrees (In.)	8
Round at 45 Degrees (In.)	6-1/2
Rectangle at 90 Degrees (In.)	14 x 8 and 2 x 14
Rectangle at 45 Degrees (In.)	6-1/2 x 6 and 2 x 7
Vise Swivels (Deg.)	45°
Blade Speeds (SFPM)	135, 197, 256
Blade Wheel Diameter (In.)	12
Blade Length (In.)	97
Blade Size (In.)	3/4 x .035 x 97
Bed Height (In.)	26
Motor (HP)	1 HP, 115/230V, 1Ph
Weight (Lbs.)	363
Overall Dimensions (L x W x H) (In.)	51-1/2 x 18-1/8 x 44



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE