

J-7020, 10" X 16" HORIZONTAL BANDSAW

414472

Exclusive 6-point blade guide assemblies and swivel control panel on this rugged JET saw enhance overall function and



FEATURES

- For added safety, the J-7020 follows strict guidelines and electrical requirements to be certified by CSA Group
- Swing away control panel houses major saw controls
- Variable speed drive system allows the operator to easily fine tune the blade speed
- Adjustable blade guide with six contact point system that utilizes cam follower bearings mounted on eccentric shafts on both sides of the blades
- Heavy-Duty transmission utilizes hardened and ground gears operating in an oil bath
- Patented 3-Jaw vise with rapid action moveable jaw for faster set up
- One-piece wheel cover
- Coolant system
- Cast iron blade wheels
- Adjustable material stop
- 1" Bi-metal blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-7020, 10" X 16" HORIZONTAL BANDSAW

414472

SPECIFICATIONS

Cutting Capacity (W x D) (In.)	10 x 16
Round at 90 Degrees (In.)	10
Round at 45 Degrees (In.)	10
Rectangle at 90 Degrees (In.)	10 x 10 and 7 x 16
Rectangle at 45 Degrees (In.)	6-1/2 x 11
Vise Swivels (Deg.)	45°
Blade Speeds (SFPM)	100 - 350
Blade Wheel Diameter (In.)	14
Blade Length (In.)	130
Blade Size (In.)	1 x .035 x 135
Bed Height (In.)	23-1/2
Motor (HP)	1-1/2 HP, 115/230V, 1Ph
Weight (Lbs.)	927
Overall Dimensions (L x W x H) (In.)	75-1/2 x 33 x 41



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE