

J-7040M, 10" X 16" HORIZONTAL MITERING BANDSAW

414475

JET Mitering Horizontal bandsaws unique design features a swiveling head while the base remains stationary. This allows the stock to remain same position while making accurate crosscuts and miters. Backed by the industry leading two year warranty, JET Mitering Bandsaws are built to last and deliver precision results.



FEATURES

- Mitering head swivels to cut any angle 0° - 45° while the work piece remains secured
- Swing away control panel houses major saw controls
- Variable speed drive system allows the operator to easily fine tune the blade speed
- Adjustable blade guide with six contact point system that utilizes cam follower bearings mounted on eccentric shafts on both sides of the blades
- The blade rides on two load bearings mounted on a pivot shaft with the side bearings and carbide pads assisting in distributing the load equally
- Downfeed system is controlled by a dual system of counterbalance springs working with a hydraulic cylinder
- Heavy-Duty transmission utilizes hardened and ground gears operating in an oil bath
- Cast Iron blade wheels
- Coolant system
- Adjustable material stop
- 1" Bi-Metal blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-7040M, 10" X 16" HORIZONTAL MITERING BANDSAW

414475

SPECIFICATIONS

Cutting Capacity (W x D) (In.)	10 x 16
Round at 90 Degrees (In.)	10
Round at 45 Degrees (In.)	8-1/2
Rectangle at 90 Degrees (In.)	10 x 14 and 2 x 16
Rectangle at 45 Degrees (In.)	8-1/2 x 9
Vise Swivels (Deg.)	45°
Head Movement (Deg.)	45°
Blade Size (In.)	1 x .035 x 135
Blade Length (In.)	135
Blade Wheel Diameter (In.)	14
Blade Speed (SFPM)	100 - 350
Bed Height (In.)	25-1/2
Motor (HP)	2 HP, 230/460, 3Ph
Drive	Variable Speed
Overall Dimensions (L x W x H) (In.)	76 x 30 x 48
Weight (Lbs.)	924



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE