

# J-7060, 12" X 20" SEMI-AUTOMATIC HORIZONTAL BANDSAW

414476

This JET large capacity variable speed semi-automatic horizontal bandsaw is loaded with features that allow the operator the ability to fine tune the blade speed easily and quickly on a convenient swing away control panel. The sturdy head raises automatically after each cut and cast iron band wheels give you the confidence of quality cuts, first time, every time.



## FEATURES

- Swing away control panel houses major saw controls
- Adjustable blade guide with six contact point system that utilizes cam follower bearings mounted on eccentric shafts on both sides of the blades
- Downfeed system is controlled by a dual system of counterbalance springs working with a hydraulic cylinder
- Saw head raises hydraulically after each cut
- Variable speed drive system allows the operator to easily fine tune the blade speed
- Heavy-Duty transmission utilizes hardened and ground gears operating in an oil bath
- Cast Iron blade wheels
- Patented 3-Jaw vise with rapid action moveable jaw for faster set up
- Coolant system
- Adjustable material stop
- 1" Bi-Metal blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-7060, 12" X 20" SEMI-AUTOMATIC HORIZONTAL BANDSAW

414476

## SPECIFICATIONS

Cutting Capacity (W x D) (In.)	12 x 20
Round at 90 Degrees (In.)	12
Round at 45 Degrees (In.)	12
Rectangle at 90 Degrees (In.)	12 x 20
Rectangle at 45 Degrees (In.)	12 x 12
Vise Swivels (Deg.)	45°
Blade Speeds (SFPM)	82 - 262
Blade Wheel Diameter (In.)	17
Blade Length (In.)	156
Blade Size (In.)	1 x .035 x 156
Bed Height (In.)	26-1/4
Motor (HP)	3 HP, 230/460V, 3Ph
Weight (Lbs.)	1,210
Overall Dimensions (L x W x H) (In.)	87 x 37-1/2 x 53



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE