

# HN-16T, BENCH HAND NOTCHER

756016

JET's high quality cast iron sheet metal notcher is ideal for any garage or sheet metal shop. Its compact design makes it perfect for on-site use. The cutting angle is fixed at ninety degrees and can notch up to 6" x 6" in one manual stroke



## FEATURES

- HAND NOTCHER
- Made of cast iron
- Capable of notching virtually any shearable material
- Can notch angles of more than 90° through a two-step process
- Easy-to-read front gauges
- Heavy-duty cutting blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# HN-16T, BENCH HAND NOTCHER

756016

## SPECIFICATIONS

Cutting Capacity (Gauge)	16
Piercing Capacity (Gauge)	18
Maximum Notch (In.)	6 x 6
Stroke (In.)	3/4
Overall Dimensions (L x W xH) (In.)	24 x 21 x 26
Weight (Lbs.)	165



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE