



J&D Manufacturing



LEADERS IN MOVING THE WORLD'S AIR

60" Premium Indoor/Outdoor UL507 Ceiling Fan

The J&D Indoor/Outdoor ceiling fan provides a healthier, cooler environment for your plants and animals all year long. In the summer the fan creates a mild wind chill to gently cool. It vertically mixes warm stagnant air and disperses hot pockets which can be a breeding ground for germs and bacteria. In the winter the fan prevents warm air from collecting in the rooftop and peaks to reduce condensation that drips down on animals, plants, and bedding surfaces.

Throughout the year, the J&D CF60A ceiling fan dries litter and bedding, walls and floors. It continuously mixes air to save you money on heating and cooling bills. Continuous circulation dissipates ammonia, gasses, and odors to keep the air not only cooler, but fresher too.

Smooth • Quiet • Efficient

Limited Lifetime Warranty on Motor



Meets UL507 wet listed standards

Features:

- Designed for high-humidity and high-moisture applications including poultry, swine, dairy, greenhouse, and factories
- UL/CUL certified (file # E130543) for outdoor and agricultural use
- Passed UL/CUL water spray test and corrosion test
- Switch on fan allows you to reverse operation for upward or downward airflow
- Completely sealed motor and housing
- 23" cord with 3-prong plug pre-wired for 115 Volts
- 10" down rod (total fan height is 21")
- High output curved steel blades
- Corrosion-resistant white powder coated finish
- Simple J-Hook Mount
- Energy efficient 9,415 CFM of air movement using less energy than a 100 Watt light bulb
- Dries litter and bedding
- Mixes air to save you money on heating and cooling bills

Variable Speed Fan Controls

Part#	Size	Wired Volts	Amps	HZ	Phs	Spd	CFM	RPM	Blade	Down Rod	Cord
CF60A	60"	115	.74	60	1	S/Var^	9,415	330	Curved	10"	23"

^ Variable speed fans require separate variable speed control to adjust fan speed.

Part#	Description	Volts	Amps
CN25	2 Fan Speed Control	120	2.5
CN5	4 Fan Speed Control	120	5
VFT130144	8 Fan Speed Control	120	10
CN15	12 Fan Speed Control	120	15