

Fiber Optic Illuminators

The Alpha 1502 fiber optic illuminator produces 150-watt shadow-free cold illumination. The easy-access hinged bulb door allows you to change a bulb or insert one of the included colored filters with ease. Choose from either the dual gooseneck light guide (which includes focusing tips) or the ring light illuminator. The unit also includes special heat blocking guards to keep the unit cool and safe.

LAMP

EKE 150W 21V quartz halogen
40,000 foot candles
200 hours at full intensity
3200°K

ELECTRONICS

Voltage: 85-265V 50-60Hz
(automatic switching)
Variable Intensity Control (0-100%)
Fuse: 3.15 amp
Low-heat solid state electronics

FEATURES

Unit remains cool to the touch during use
Heat-blocking IR glass lters installed
Compact and lightweight
Internal cooling fan

DIMENSIONS AND WEIGHT

Height: 5.5" (178mm)
Length: 10.5" (267mm)
Width: 7" (127mm)
Weight: 6lbs. (2.7kg)



Alpha 1502

Model #	Description
ILP-1502-LTS1	Alpha 1502 150w fiber optic light source
ILP-1502-DGGF	Dual gooseneck light guide with focusing tips for Alpha 1502
ILP-1502-RLG7	Ring light guide for Alpha 1502



P 770.270.1394
F 770.270.2389

865 Marathon Parkway
Lawrenceville GA 30046

LWScientific.com