# MicroMax® NS



**Dry Particulate** 













# Microporous protection from dirt, grease, grime and light chemical splash!

This line of general purpose protective clothing can be used in work environments where hazardous or non-hazardous contaminants may be present. Very economical and lightweight, MicroMax® NS features high MVTR and is breathable for worker comfort. MicroMax® NS is strong, wet or dry, perfect for work environments where dirt, grime, splashes and spills are present.

# MicroMax® NS Physical Properties

Physical Property	Test Method	Units	Test Results
Basis Weight	ASTM D3776	oz/y <sup>2</sup>	1.55 oz/y <sup>2</sup>
Grab Tensile MD	ASTM D5034	lbs.	22.0 lbs.
Grab Tensile XD	ASTM D5034	lbs.	14.0 lbs.
Trapezoidal Tear MD	ASTM D1117	lbs.	9.0 lbs.
Trapezoidal Tear CD	ASTM D1117	lbs.	5.8 lbs.
Ball Burst	ASTM D3787	lbs.	19.0 lbs.
Air Permeability	ASTM D737	cfm	<0.562 cfm/ft <sup>2</sup>
Surface Resistivity	EN1149-5:2006	Ω	Pass

### MicroMax® NS ASTM F903 Penetration Data

Chemical Tested	Concentration %	Test Time – Minutes	Test Results
Diazinon	100%	60	Pass
Motor Oil-40 wt.	100%	60	Pass
Bleach-household	100%	60	Pass
Isocyanate Based Paint	100%	60	Pass
Sodium Hydroxide	50%	60	Pass
Sodium Hyperchlorite	10%	60	Pass
Blood	Challenge Fluid Liter — 3.20 x 108 (PFU/mL)	Assay Results PFU/mL <1	Pass



800-645-9291 | 256-350-3873 Email: info@lakeland.com www.lakeland.com



# Labcoat **CTL101**

- Snap closure
- 2 pockets

· Long sleeve Sizes: S – 5X Case Pack: 30



### Labcoat **CTL104**

- · Snap closure
- 2 pockets
- Long sleeve

• Elastic wrists

**Sizes**: S − 5X

Case Pack: 30



### Labcoat **CTL112**

- Snap closure
- No pockets
- Long sleeve
- Elastic wrists

**Sizes**: S − 5X Case Pack: 30



# Labcoat CTL140

- Snap closure
- No pockets
- · Long sleeves.

**Sizes**: S − 5X Case Pack: 30



### Frock **CTL190**

- · Mandarin collar
- 5 snaps
- No pockets
- Elastic wrists


**Sizes**: S − 5X Case Pack: 30



# Frock **CTL191**

- Mandarin collar
- Zipper closure
- No pockets • Elastic wrists


Sizes: S - 5XCase Pack: 25



# Shirt **CTL201**

- Snap closure Long sleeves
- Sizes: S 5X

Case Pack: 50



Pants CTL301

• Elastic waist Sizes: S – 5X Case Pack: 50



### Coverall **CTL412**


 Zipper closure **Sizes**: S − 5X Case Pack: 25



### Coverall **CTL414**

- Zipper closure
- Attached hood
- Boots
- Elastic wrists Sizes: S - 5X

Case Pack: 25





- Zipper closure
- Elastic wrists
- Elastic ankles

Sizes: S - 5X

Case Pack: 25



### Coverall **CTL428**

- Zipper closure
- Attached hood
- Elastic wrists
- Elastic ankles

**Sizes**: S − 5X

Case Pack: 25



### Smock CTL501

- Long sleeves
- Attached ties

Sizes: S - 5X


Case Pack: 50



# Apron CTL601

• Sewn ties Sizes: 28"w x 36"l


Case Pack: 100



### Apron CTL603


Sewn ties

Sizes: 28"w x 44"l Case Pack: 100




### Hood CTL701

- Drawstring closure
- One size Case Pack: 250




### Hood **CTL713**

- Elastic face
- Covers shoulders
- One size Case Pack: 250



### Sleeve **CTL850**

• Elastic ends Sizes: 18" length Case Pack: 100 pair



### **Shoe Cover** CTL901 901NS (non-skid)

- Elastic ankles
- Style 901 standard version
- Style 901NS gray non-skid version

Sizes: S/M, L/XL, 2X Case Pack: 200 pair



# **Boot Cover** CTL903 903NS (non-skid)

- Elastic top
- 17" high
- Style 903 standard version
- Style 903NS gray non-skid version

Sizes: S/M, L/XL, 2X Case Pack: 200 pair



# **Shoe Cover CTL904**

 Vinyl sole Sizes: S/M, L/XL, 2X Case Pack: 200 pair



### **Boot Cover CTL905**

- Elastic top
- 17" high
- · Vinyl sole

Sizes: S/M, L/XL, 2X Case Pack: 200 pair