



Outstanding Quality Products
Competitive Prices
Superior Service

MILESYN SXR 0W20

EXTENDED LIFE FORMULA FULL SYNTHETIC MOTOR OIL

MILES FULL SYNTHETIC MOTOR OIL 0W20 is specifically formulated for and licensed by General Motors to meet their new Global Engine Oil Specification. This premium synthetic motor oil is produced with a proprietary blend of high performance synthetic base stocks along with a proprietary component system that is licensed and approved by General Motors. This oil meets or exceeds the latest API SN and ILSAC GF-5 specifications as well as all previous service classifications, API SM, SL and ILSAC GF-4 and GF-3.

This is premium quality motor oil designed to meet the most demanding lubrication requirements of today's naturally aspirated, turbo-charged and super-charged gasoline fueled engines. It is specially formulated to provide excellent oxidation stability, increase wear protection, excellent low temperature flow properties, reduce oil consumption and enhance fuel economy. License No. D10024GB141.

Recommended for Applications

- API SN,
- SM, SL SJ
- ILSAC GF-5
- GF-4, GF-3
- ACEA A1

Typical Properties

| Property | 0W20 |
|---------------------------|-------|
| Density | 7.10 |
| Viscosity, cSt @ 100°C | 8.2 |
| Viscosity, cSt @ 40°C | 43 |
| Viscosity, CCS cP @ -35°C | 5600 |
| High Temp./High Shear | 2.6 |
| Viscosity Index | 170 |
| Flash Point, °C | 220 |
| Pour Point, °C | -51 |
| Zinc. Wt. (%) | 0.084 |
| Phosphorous, Wt. (%) | 0.074 |
| Calcium, Wt. (%) | 0.215 |
| NOACK, Wt. (%) | 12.5 |