

# MILESYN SXR 5W30

## EXTENDED LIFE FORMULA FULL SYNTHETIC MOTOR OIL

**MILES FULL SYNTHETIC MOTOR OIL 5W30** is designed to meet or exceed the requirements specified for gasoline fueled GM vehicles produced after 2011. This premium synthetic motor oil is produced with a proprietary blend of high performance synthetic base stocks along with a proprietary component system that is licensed and approved by general motors. This fluid is designed to perform under extreme conditions where excellent cold temperature properties and thermal breakdown resistance are required. The oil also exceeds the performance requirements of ILSAC GF-5 fluids. License # D10022GB141.

### Features and Benefits

- Formulated for superior engine protection
- Extremely low volatility
- Excellent Oxidation Stability
- Excellent protection against sludge and varnish
- Highly resistant to foaming and corrosion
- Improves oil film strength and breakdown resistance

### Recommended for Applications

- API SN
- ILSAC GF-5
- GM 6094M, 4718M
- FORD MCC153H, M2C929-A

## Applications

**MILES FULL SYNTHETIC MOTOR OIL 5W30** is recommended for all types of modern vehicles, including high-performance turbocharged, supercharged gasoline and diesel multi-valve fuel injection engines found in passenger cars, SUV's, light vans and trucks. This fluid is backward compatible for all GM vehicles.

## Typical Properties

Property	5W30
Density	7.10
Viscosity, cSt @ 100°C	11.0
Viscosity, cSt @ 40°C	63.0
Viscosity, CCS cP @ -30°C	5200
High Temp./High Shear	3.1
Viscosity Index	165
Flash Point, °C	220
Pour Point, °C	-45
NOACK, Wt. (%)	11.0