


Configuration of NBS0416BW Smoking Shelter

issue 4

Component	Part No	Item	Length	No
Uprights Double	A48FS-1C	1	2000	2
Uprights Corner	A48FS-2C	2	2000	1
Uprights Single LH	A48FS-3C	3	2000	2
Uprights Single RH	A48FS-3aC	3a	2000	2
Horizontals Full Bay	A48FS-8	4	998	5
Roof Ends x1	A48FS-6	5		2
Roof Middle Single	A412FS-1	5M		2
Roof Side 4 Bay Box	A416FS-4LH	7	2072	2
Roof Side 4 Bay Box	A416FS-4RH	7a	2072	2
Roof End x1Box	A48FS-5	8	998	2
Centre Tie Bar x1	A416FS-5	13	1074	1
C type Glazing Bead	A48FS-13	9	1792	10
Roof Support Bar	A412FS-12	10	600	1
Plastic Glazing Panels "C"	NBB910	1808x988		5
Std Foot "L" Assembly	A48FS-16	12		7
End Caps Square	NBB903			6
Roof Trim	A48FS-12			3
Hex Head Drill Screws (small)	NBB901			9
Anchor Bolts	NBB915			7
Paint Stick	NBB914			1
Top Bracket (Stud)	A48FS-15	14		4
Top Bracket (Thread)	A48FS-16	16		3
M8 x 50 allen bolt	NBB906			3
Hex Head Drill Screws	NBB907			45
M6x12 poz screws	NBB902			14
M8x12 screw & washer	NBB909			7



Layout of Uprights & Roof Fixing NBS0A416BW

Type of upright	Type of Top Bracket	No
Uprights Single LH	Top Bracket (Stud)	1
Uprights Single RH	Top Bracket (Stud)	2
Uprights Single LH	Top Bracket (Stud)	3
Uprights Corner	Top Bracket (Stud)	4
Uprights Double	Top Bracket (Thread)	5
Uprights Double	Top Bracket (Thread)	6
Uprights Single RH	Top Bracket (Thread)	7

