

Hose Clamp 3285

| Size (D) In. | Weight Lbs | 304SS |
|-----------------|---------------|-------|
| | | 16ga |
| 2 | 0.05 | Std |
| 3 | 0.06 | |
| 4 | 0.07 | |
| 5 | 0.08 | |
| 6 | 0.09 | |
| 7 | 0.10 | |
| 8 | 0.14 | |
| 9 | 0.15 | |
| 10 | 0.17 | |
| 12 | 0.20 | |
| 14 | 0.25 | |
| 16 | 0.30 | |
| 18 | 0.40 | |
| 20 | 0.45 | |
| 22 | 0.50 | |
| 24 | 0.60 | |

| Temperature Rating of Product Components | |
|--|------------|
| ° F | Hose Clamp |
| 1100° | 304SS |
| -40° | |

| Additional Notes |
|--|
| 304SS: bluing may occur at 800° F and above |

| Compliance / Rating of Product Components | | |
|---|----------|------------------------|
| Product | Material | Compliance / Rating |
| Hose Clamp | 304SS | Finish meets ASTM A240 |

Construction:

1/2" band and housing components: stainless steel
 Slotted 5/16" hex head screw: 400 series stainless steel
 100% interlock construction features one piece housing which directly locks into the band and spot weld free design.
 Meets or exceeds SAE torque specifications.

